



Horizontal Pin Standoff Bracket, 36" Two-Phase

By Chance

Catalog # [2SBM36HH4](#)



36" Medium Duty Fiberglass Two-Phase Horizontal Pin Standoff Bracket with 1.375" Lead Threads

*Representative Image

General

Catalog Number	2SBM36HH4
Description - End Fitting	Horizontal Pin
Material - Threads	1.375" Lead Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1200 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359069423

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Length	36 in
Mounting Bolt Spacing	5 in
	6 in
	8 in
Weight	9.8 lb

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)



A Hubbell brand