



Horizontal Pin Standoff Bracket, 40" Two-Phase

By CHANCE Utility
Catalog # [2SBM40HH3](#)



40" Medium Duty Fiberglass Two-Phase Horizontal Pin Standoff Bracket with 1" Lead Threads

*Representative Image

General

Description - End Fitting	Horizontal Pin
Material - Threads	1" Lead Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1000 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1000 lb
UPC	096359069485

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	40 in
Length	40.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 5.00 in• 6.00 in• 8.00 in
Weight	15.8 lb

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-30\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-2SBM40HH3-SPEC-EN | REV 1/2024