



15° 4-Hole Cloverleaf Cutout / Arrester Standoff Bracket, 42" 2- Phase

By Chance

Catalog # [2SBM42CLCL](#)

42" Medium Duty Fiberglass 15° 4-Hole Cloverleaf Two-Phase
Cutout / Arrester Standoff Bracket



*Representative Image

General

Catalog Number	2SBM42CLCL
Description - End Fitting	3 Position Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	950 lb
UPC	096359595823

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	42 in
Length	42 in
Mounting Bolt Spacing	5 in
	6 in
	8 in
Weight	13.3 lb

Electrical Ratings

Phase	2-Phase
-------	---------

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)



A Hubbell brand