



Vertical Pin Standoff Bracket, 44" Two-Phase

By CHANCE Utility
Catalog # [2SBM44VV4](#)



*Representative Image

44" Medium Duty Fiberglass Two-Phase Vertical Pin Standoff Bracket with 1.375" Lead Threads

General

Description - End Fitting	Vertical Pin
Material - Threads	1.375" Lead Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	725 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1225 lb
UPC	096359360032

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	44 in
Length	44.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 5.00 in• 6.00 in• 8.00 in
Weight	14.0 lb

Logistics

Standard Package 3

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-29\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-2SBM44VV4-SPEC-EN | REV 1/2024