



15° 4-Round Holes Cloverleaf Cutout / Arrester Standoff Bracket, 36" 13" 3-Phase

By Chance
Catalog # [3SBM3613CLRH](#)



36" 13" Medium Duty Fiberglass 15° 4-Round Holes Cloverleaf
Three-Phase Cutout / Arrester Standoff Bracket

*Representative Image

General

Catalog Number	3SBM3613CLRH
Description - End Fitting	3 Position Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10,000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1,200 lb
UPC	096359572008

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Distance from Pole - Third Phase	13 in
Length	36 in
Mounting Bolt Spacing	6 in
	8 in
Weight	20 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Carton Quantity	3
Standard Package	5

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)
[Sales Drawings - Standoff Cloverleaf](#)