



0° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware & Spacer Bars(No Collars), 36" 13" 3-Phase

By CHANCE Utility
Catalog # [3SBM3613SGLSB](#)



*Representative Image

36" 13" Medium Duty Fiberglass 0° 2-Position Cutout / Arrester 3-Phase Standoff Bracket w/ Hardware & Spacer Bars (No Collars)

General

Description - End Fitting	1 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	5000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359614609

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Distance from Pole - Third Phase	13 in
Length	36.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> • 6.00 in • 8.00 in
Weight	11.9 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Standard Package	5
------------------	---

Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-55\)](#)
- [Sales Drawings - 1 \(2\) Position \(0°\) Three-Phase \(SA3SBM3613SGLSB\)](#)



A proud member of the Hubbell Family.