



15° 1-Position Cutout / Arrester  
Standoff Bracket, 36" 18" Three-  
Phase (No Hardware or Collars)

By CHANCE Utility  
Catalog # 3SBM3618AM



\*Representative Image

General

Description - End Fitting	1 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359498889

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Distance from Pole - Third Phase	18 in
Length	36.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>6.00 in</li><li>8.00 in</li></ul>
Weight	12.2 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Carton Quantity	5
Standard Package	5

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-56\)](#)



A proud member of the Hubbell Family.