



15° 4-Hole Cloverleaf Cutout / Arrester Standoff Bracket, 36" 18" 3-Phase w/ Hardware

By CHANCE Utility
Catalog # [3SBM3618CLH](#)



*Representative Image

General

Description - End Fitting	3 Position Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10,000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1,200 lb
UPC	096359399148

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Distance from Pole - Third Phase	18 in
Length	42.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 6.00 in• 8.00 in
Weight	22.0 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Carton Quantity	10
Standard Package	5

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-63\)](#)
[Catalogs - CHANCE® Fiberglass Construction Products \(Catalog 12\)](#)
[Sales Drawings - 3 Position, 3 Phase Standoff Bracket \(SA3SMBxxxxCLH\)](#)



A proud member of the Hubbell Family.