



## 0° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware, 36" 18" Three-Phase

By CHANCE Utility  
Catalog # [3SBM3618CTB](#)



36" 18" Medium Duty Fiberglass 0° 2-Position Three-Phase Cutout / Arrester Standoff Bracket w/ Hardware

\*Representative Image

### General

Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	900 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359396093

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Distance from Pole - Third Phase	18 in
Length	36.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>6.00 in</li><li>8.00 in</li></ul>
Weight	22.0 lb

### Electrical Ratings

Phase	3-Phase
-------	---------

### Logistics

Carton Quantity	5
Standard Package	5

### Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-60\)](#)
- [Catalogs - CHANCE® Fiberglass Construction Products \(Catalog 12\)](#)
- [Sales Drawings - Standoff, 3 Phase, 0° "T" End Fitting \(SA3SBM3613CT\)](#)
- [Sales Drawings - Standoff "T" End Fitting \(SA3SBM3613CT\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-3SBM3618CTB-SPEC-EN | REV 4/2023