



0° 1-Position Cutout / Arrester Standoff Bracket (No Hardware or Collars), 36" 18" 3-Phase

By CHANCE Utility
Catalog # [3SBM3618SGL](#)



36" 18" Medium Duty Fiberglass 0° 1-Position Cutout / Arrester 3-Phase Standoff Bracket (No Hardware or Collars)

General

Description - End Fitting	1 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	5000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359652267

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Distance from Pole - Third Phase	18 in
Length	36.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 6.00 in• 8.00 in
Weight	12.6 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Standard Package	5
------------------	---

Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-53\)](#)
- [Sales Drawings - 1 \(2\) Position \(0°\) Three-Phase \(SA_3SBM3613SGL\)](#)
- [Technical Solutions - CH-3SBM3618SGL-SPEC-EN](#)



A proud member of the Hubbell Family.