



Vertical Pin Standoff Bracket, 40" 28" Three-Phase

By CHANCE Utility
Catalog # [3SBM4028VV4](#)

40" 28" Medium Duty Fiberglass Three-Phase Vertical Pin Standoff Bracket with 1.375" Lead Threads



*Representative Image

General

Description - End Fitting	Vertical Pin
Material - Threads	1.375" Lead Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1350 lb

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	40 in
Distance from Pole - Third Phase	28 in
Length	40.00 in
Mounting Bolt Spacing	8.00 in
Weight	19.4 lb

Logistics

Standard Package	5
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-31\)](#)
[Technical Solutions - CH-3SBM4028VV4-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-3SBM4028VV4-SPEC-EN | REV 1/2024