



0° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware, 48" 13" Three-Phase

By Chance
Catalog # [3SBM4813CTB](#)

48" 13" Medium Duty Fiberglass 0° 2-Position Three-Phase Cutout / Arrester Standoff Bracket w/ Hardware

Features

- 2 position "T" bracket with hardware (captive bolt, nut, and washers)
- 1.5" (medium duty) fiberglass rod
- 0° angle
- Base and end fittings are aluminum alloy

General

Catalog Number	3SBM4813CTB
Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359366768

Dimensions

Diameter - Rod / Tube	1.5 in
Dimensions	48 in x 10 in x 15 in
Distance From Pole	48 in
Distance from Pole - Third Phase	13 in
Height	15 in



Length	48 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 6 in• 8 in
Weight	20 lb
Width	10 in

Electrical Ratings

Phase	3-Phase
-------	---------

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Carton Quantity	5
Pallet Quantity	5
Standard Package	5

Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Catalogs - CHANCE® Fiberglass Construction Products](#)
- [Sales Drawings - Standoff "T" End Fitting](#)
- [Sales Drawings - Standoff, 3 Phase, 0° "T" End Fitting](#)
- [Specifications - 3SBM4813CTB](#)



A Hubbell brand