



## 0° 1-Position Cutout / Arrester Standoff Bracket w/ Hardware (No Collars), 48" 13" 3-Phase

By Chance

Catalog # [3SBM4813SGLB](#)



48" 13" Medium Duty Fiberglass 0° 1-Position Cutout / Arrester 3-Phase Standoff Bracket w/ Hardware (No Collars)

\*Representative Image

### General

Catalog Number	3SBM4813SGLB
Description - End Fitting	1 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	5000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359521686

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	48 in
Distance from Pole - Third Phase	13 in
Length	48 in
Mounting Bolt Spacing	6 in
	8 in
Weight	13.5 lb

### Electrical Ratings

Phase	3-Phase
-------	---------

### Logistics

Standard Package	5
------------------	---

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)

[Sales Drawings - SA3SBMxxxxSGLB](#)