



## 15° 1-Position Cutout / Arrester Standoff Bracket, 48" 18" Three-Phase (No Hardware or Collars)

By CHANCE Utility  
Catalog # [3SBM4818AM](#)



48" 18" Medium Duty Fiberglass 15° 1-Position Three-Phase Cutout / Arrester Standoff Bracket (No Hardware or Collars)

\*Representative Image

### General

Description - End Fitting	1 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359712732

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	48 in
Distance from Pole - Third Phase	18 in
Length	48.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 6.00 in</li><li>• 8.00 in</li></ul>
Weight	14.4 lb

### Electrical Ratings

Phase	3-Phase
-------	---------

### Logistics

Standard Package	5
------------------	---

### Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-56\)](#)  
[Technical Solutions - CH-3SBM4818AM-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-3SBM4818AM-SPEC-EN | REV 1/2024