



# 15° 4-Hole Cloverleaf Cutout / Arrester Standoff Bracket, 48" 18" 3-Phase w/ Hardware

By Chance

Catalog # [3SBM4818CLH](#)



48" 18" Medium Duty Fiberglass 15° 4-Hole Cloverleaf Three-Phase Cutout / Arrester Standoff Bracket w/ Hardware

\*Representative Image

## Features

CLH Series includes bolt, nut and washers

## General

Catalog Number	3SBM4818CLH
Description - End Fitting	3 Position Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10,000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359400073

## Dimensions

Diameter - Rod / Tube	1.5 in
Dimensions	48.00 in x 9 in x 4.1 in
Distance From Pole	48 in
Distance from Pole - Third Phase	18 in
Height	4.1 in
Length	48 in
Mounting Bolt Spacing	6 in
	8 in
Weight	20 lb
Width	9 in

## Electrical Ratings

Phase	3-Phase
-------	---------

## Logistics

Carton Quantity	5
Pallet Quantity	5
Standard Package	5

## Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products](#)  
[Catalogs - CHANCE® Fiberglass Construction Products](#)  
[Sales Drawings - 3 Position, 3 Phase Standoff Bracket](#)



A Hubbell brand