



0° 2-Position Cutout / Arrester Standoff Bracket w/ Hardware, 48" 18" Three-Phase

By CHANCE Utility
Catalog # [3SBM4818CTB](#)



48" 18" Medium Duty Fiberglass 0° 2-Position Three-Phase Cutout / Arrester Standoff Bracket w/ Hardware

*Representative Image

General

Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359398417

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	48 in
Distance from Pole - Third Phase	18 in
Length	48.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 5.00 in• 6.00 in• 8.00 in
Weight	25.0 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Pallet Quantity	5
Standard Package	5

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-60\)](#)
[Catalogs - CHANCE® Fiberglass Construction Products \(Catalog 12\)](#)
[Sales Drawings - Standoff, 3 Phase, 0° "T" End Fitting \(SA3SBM3613CT\)](#)
[Sales Drawings - Standoff "T" End Fitting \(SA3SBM3613CT\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-3SBM4818CTB-SPEC-EN | REV 7/2023