



## 2 Ton Ratchet Link Chain Hoist

By CHANCE Utility  
Catalog # 4012

Every CHANCE Chain Hoist is proof-tested and factory-operated at 150% of capacity rating. Lightweight high-strength handle and sheave housings are heat-treated aluminum.



### Features

- All working parts fully enclosed in housing
- Polished high-strength alloy steel chain
- Forged steel 360° swivelling load hooks with spring-loaded latches
- Controls automatically lock when under load
- Ratchet handle swings to either side
- Lifetime oil-impregnated bronze sleeve bearings require no additional lubrication

### General

Application - For Use On	90.0 lb., 40.8 kg
Connector	11 in, 27.9 cm
Strength Rating - Ultimate	4000 lb
Style	Link Chain Hoist
UPC	096359071778

### Dimensions

Dimensions	20 in x 7.87 in x 6.87 in
Height	6.87 in
Length	20 in
LengthMetric	50.8 mm
Weight	28.5 lb
WeightMetric	12.9 kg
Width	7.87 in

### Logistics

Pallet Quantity	28
Standard Package	1

### Product Assets

[Catalogs - Mechanical Hoists \(1100\)](#)  
[Installation Manuals - Ratchet Link Chain Hoists \(TD09232E\)](#)  
[Literature - Tips of the Trade - Hoist Safety \(BR09004E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-4012-SPEC-EN | REV 7/2023