



## BOLT, THIMBLEYE, ANGLE, 5/8in x 14in

By Chance  
Catalog # 5014

Used in down guy applications for loop-type deadend attachments.



### Features

- 4" thread length and cone pointed end
- Includes one square nut
- Internal eye dimensions are 9/16" x 11/16"
- Rated tensile strength is 12,400 lbs.
- Hot dip galvanized per ASTM A-153
- RUS listed, ao - Bolt, strand eye, straight (thimble eye)

### General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb.
Type	Thimbleye Bolts
UPC	096359072171

### Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Distance From Pole	N/A
Length	14 in
Length - Threaded Area	6 in
Weight	1.8 lb

### Certifications And Compliance

Industry Standard(s)	ANSI 135.4
----------------------	------------

### Logistics

Pallet Quantity	1250
-----------------	------

### Product Assets

[Catalogs - Communications Catalog](#)  
[Sales Drawings - 5/8" Angle Thimbleye Bolt](#)



A Hubbell brand