



Oh No!
IMAGE COMING SOON

BOLT, THIMBLEYE, ANGLE, 5/8in x 14in

By Chance
Catalog # 5014

Used in down guy applications for loop-type deadend attachments.

Features

- 4" thread length and cone pointed end
- Includes one square nut
- Internal eye dimensions are 9/16" x 11/16"
- Rated tensile strength is 12,400 lbs.
- Hot dip galvanized per ASTM A-153
- RUS listed, ao - Bolt, strand eye, straight (thimble eye)

General

Catalog Number	5014
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb.
Type	Thimbleye Bolts
UPC	096359072171

Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Distance From Pole	N/A
Length	14 in
Length - Threaded Area	6 in
Weight	1.8 lb

Certifications And Compliance

Industry Standard(s)	ANSI 135.4
----------------------	------------

Logistics

Pallet Quantity	1250
-----------------	------

Product Assets

- [Catalogs - Communications Catalog](#)
- [Sales Drawings - 5/8" Angle Thimbleye Bolt](#)
- [Specifications - 5014](#)



A Hubbell brand