



Rod, Expanding/Cross-Plate Anchor, 5/8in X 7ft Thimbleye

By Chance
Catalog # 5317

Expanding/Cross-Plate Anchor Rod 0.625" (15.9 mm) Diameter Rod, 7' (2134 mm) long with Thimbleye.



Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153
- Square nut assembled to rod
- Rods used with Cross-plate and Expanding anchors

General

Application	Earth Tension Anchoring
Catalog Number	5317
Coating	Galvanized, ASTM A-153
Eyenuit Style	Thimbleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	16000 lb.
Type	Anchor Rod
UPC	096359072362

Dimensions

Dimensions	84.000 in x 0.650 in x 1.000 in
Height	1 in
Length	84 in
Rod Diameter	0.625 in
Weight	7.448 lb
Width	0.65 in

Certifications And Compliance

Industry Standard(s)	NEMA Standard
RUS Listed Reference	x - Rod, anchor

Logistics

Pallet Quantity	100
Standard Package	5

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06136E_Cross_Plate_Anchors](#)
- [Installation Manuals - TD06135E_Expanding_Anchors](#)
- [Literature - Anchoring](#)
- [Sales Drawings - Threaded Thimbleye Rod - 5/8"](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Expanding Anchors](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-5317-SPEC-EN | REV 6/2024