



Rod, Expanding/Cross-Plate Anchor, 5/8in X 8ft Twineye

By Chance
Catalog # 5348

Expanding/Cross-Plate Anchor Rod 0.625" (15.9 mm) Diameter
Rod, 8' (2438 mm) long with Twineye.

Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading,kinking, or bending.
- Hot dipped galvanized per ASTM A153
- Square nut assembled to rod
- Rods used with Cross-plate and Expanding anchors

Application

Earth Tension Anchoring

General

Catalog Number	5348
Coating	Galvanized, ASTM A-153
Eyenum Style	Twineye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	16000 lb.
Type	Anchor Rod
UPC	096359072454

Dimensions

Dimensions	96.000 in x 0.650 in x 1.250 in
------------	---------------------------------



Height	1.25 in
Length	96 in
Rod Diameter	0.625 in
Weight	8.722 lb
Width	0.65 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Industry Standard(s)	NEMA Standard
RUS Listed Reference	x - Rod, anchor

Logistics

Pallet Quantity	100
Standard Package	5

Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Anchors](#)
- [Catalogs - Dependable Anchoring Solutions](#)
- [Catalogs - Communications Catalog](#)
- [Installation Manuals - TD06135E_Expanding_Anchors](#)
- [Installation Manuals - TD06136E_Cross_Plate_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Sales Drawings - Threaded Twineye Rod - 5/8"](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - 5348](#)
- [Video - CHANCE Expanding Anchors](#)