



Rod, Expanding/Cross-Plate Anchor, 3/4in X 9ft Twineye

By Chance
Catalog # 5359

Expanding/Cross-Plate Anchor Rod 0.75" (19.1 mm) Diameter
Rod, 9' (2743 mm) long with Twineye.

Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153
- Square nut assembled to rod
- Rods used with Cross-plate and Expanding anchors

Application

Earth Tension Anchoring

General

Catalog Number	5359
Coating	Galvanized, ASTM A-153
Eyenum Style	Twineye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	23000 lb.
Type	Anchor Rod
UPC	096359072515

Dimensions

Dimensions	108.000 in x 0.750 in x 1.250 in
------------	----------------------------------



Height	1.25 in
Length	108 in
Rod Diameter	0.75 in
Weight	13.72 lb
Width	0.75 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Industry Standard(s)	NEMA Standard
RUS Listed Reference	x - Rod, anchor

Logistics

Pallet Quantity	60
Standard Package	3

Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Anchors](#)
- [Catalogs - Dependable Anchoring Solutions](#)
- [Catalogs - Communications Catalog](#)
- [Installation Manuals - TD06135E_Expanding_Anchors](#)
- [Installation Manuals - TD06136E_Cross_Plate_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Sales Drawings - Threaded Twineye Rod - 3/4"](#)
- [Sales Drawings - Threaded Twineye Rod - 3/4"](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - 5359](#)
- [Video - CHANCE Expanding Anchors](#)



A Hubbell brand