



BOLT, THIMBLEYE, STRAIGHT, 5/8in x 10in

By Chance
Catalog # 5510

Used in deadend applications with loop-type attachments.

Features

- 4" thread length and cone pointed end
- Includes one square nut
- Internal eye dimensions are 9/16" x 11/16"
- Rated tensile strength is 12,400 lbs.
- Hot dip galvanized per ASTM A-153
- RUS listed, ao - Bolt, strand eye, straight (thimble eye)

General

Catalog Number	5510
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb.
Type	Thimbleye Bolts
UPC	096359072690

Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Dimensions	12.500 in x 0.500 in x 1.500 in



Distance From Pole	N/A
Height	1.5 in
Length	12.5 in
Length - Threaded Area	4 in
Weight	1.41 lb
Width	0.5 in

Certifications And Compliance

Industry Standard(s)	ANSI C135.1
RUS Listed Reference	ao - Bolt, strand eye, straight (thimble eye)

Logistics

Pallet Quantity	1600
-----------------	------

Product Assets

- [Catalogs - Dependable Anchoring Solutions](#)
- [Catalogs - Communications Catalog](#)
- [Sales Drawings - 5/8" Thimbleye Bolt](#)
- [Specifications - 5510](#)



A Hubbell brand