



BOLT, THIMBLEYE, STRAIGHT, 5/8in x 16in



By Chance
Catalog # [5516](#)

Used in deadend applications with loop-type attachments.

Features

- 6" thread length and cone pointed end
- Includes one square nut
- Internal eye dimensions are 9/16" x 11/16"
- Rated tensile strength is 12,400 lbs.
- Hot dip galvanized per ASTM A-153
- RUS listed, ao - Bolt, strand eye, straight (thimble eye)

General

Catalog Number	5516
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb.
Type	Thimbleye Bolts
UPC	096359072720

Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Dimensions	17.830 in x 1.500 in x 1.375 in
Distance From Pole	N/A
Height	1.375 in
Length	17.83 in
Length - Threaded Area	6 in
Weight	1.88 lb
Width	1.5 in

Logistics

Pallet Quantity	1250
-----------------	------

Product Assets

- [Catalogs - Dependable Anchoring Solutions](#)
- [Catalogs - Communications Catalog](#)
- [Sales Drawings - 5/8" Thimbleye Bolt](#)
- [Specifications - 5516](#)



A Hubbell brand