



BOLT, THIMBLEYE, STRAIGHT, 3/4in x 12in

By Chance
Catalog # 5612



Used in deadend applications with loop-type attachments.

Features

- 6" thread length and cone pointed end
- Includes one square nut
- Internal eye dimensions are 11/16" x 13/16"
- Rated tensile strength is 18,350 lbs.
- Hot dip galvanized per ASTM A-153
- RUS listed, ao - Bolt, strand eye, straight (thimble eye)

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb.
Type	Thimbleye Bolts
UPC	096359072799

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Distance From Pole	N/A
Length	12 in
Length - Threaded Area	6 in
Weight	2.35 lb

Certifications And Compliance

RUS Listed Reference	ao - Bolt, strand eye, straight (thimble eye)
----------------------	---

Logistics

Pallet Quantity	540
-----------------	-----

Product Assets

[Catalogs - Communications Catalog](#)
[Sales Drawings - 3/4" Thimbleye Bolt](#)



A Hubbell brand