



BOLT, THIMBLEYE, STRAIGHT, 3/4in x 14in

By Hubbell
Catalog # 5614



Used in deadend applications with loop-type attachments.

Features

- 6" thread length and cone pointed end
- Includes one square nut
- Internal eye dimensions are 11/16" x 13/16"
- Rated tensile strength is 18,350 lbs.
- Hot dip galvanized per ASTM A-153
- RUS listed, ao - Bolt, strand eye, straight (thimble eye)

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb.
Type	Thimbleye Bolts
UPC	096359072805

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Length	14.00 in
Length - Threaded Area	6.00 in
Weight	2.40 lb

Logistics

Pallet Quantity	600
-----------------	-----

Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)
[Sales Drawings - 3/4" Thimbleye Bolt \(SA5608\)](#)

Related Products

[C2050187 - SPRING WASHER, REGULAR-DUTY DOUBLE-COIL, 3/4in SIZE](#)
[6823 - 3in SQUARE CURVED WASHER for 3/4in BOLT SIZE, 7/8in HOLE](#)
[3513 - MF TYPE CURVED LOCK NUT, 3/4in THREAD](#)
[6814 - 2-1/4in SQUARE FLAT WASHER for 3/4in BOLT SIZE, 13/16in HOLE](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-5614-SPEC-EN | REV 1/2024