



Anchor, Tool, Kelly Bar Adapter, 2.5in Hex, 10,000 ft-lb rating

By CHANCE Utility
Catalog # [630011HD](#)

Standard Kelly Bar Adapter 10,000 Ft Lbs (13,558 N-M) for 2 1/2" (63.5 mm) Hex Kelly Bar.



Features

- Kelly Bar Adapter attaches to truck's torque motor drive shaft (Kelly Bar)
- Locking Dog Assembly has six holes for 1/2" bolts on a 5-1/4" bolt circle, comes with six 1/2" Grade 5 bolts, nuts and lock washers
- Painted with green paint
- Includes Bent Arm Pin and Coil Lock

Application

Anchor/Pile Installation

General

Bolt Grade	5
Coating	Painted
EU RoHS Indicator	No
Kelly Bar Shape	Hex
Number of Bolt Holes	6
Torque Rating	10000 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359227410

Dimensions

Anchor Installation Hole Size	0.5 in
Diameter - Bolt	0.5 in
Diameter - Bolt Circle	5.25 in
Dimensions	12.000 in x 7.630 in x 6.250 in
Height	6.250 in
Kelly Bar Adapter Inside Width	2.5 in
Kelly Bar Hole Distance to Flange	4.25 in
Length	12.000 in
Weight	17.640 lb
Width	7.630 in

Logistics

Pallet Quantity	60
Standard Package	1

Product Assets

[Catalogs - Anchor Tools \(4A_CA06122E\)\)](#)
[Installation Manuals - Instructions for CHANCE Kelly Bar Adapters \(P3031465\)](#)
[Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
[Literature - Anchoring \(CA12002E\)](#)
[Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide \(BR06167E\)](#)
[Sales Drawings - Kelly Bar Socket \(SA630011HD\)](#)
[Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

Related Products

[055635P - Anchor Tool Nut](#)
[P0010259P - Anchor Tool Bolt](#)
[C3031223 - Anchor, Tool, Bent Arm Pin, 1/2in X 4.5in](#)
[055371P - Anchor Tool Lockwasher](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-630011HD-SPEC-EN | REV 1/2024