



Anchor, Tool, Kelly Bar Adapter, 2.0in Hex, 10,000 ft-lb rating

By CHANCE Utility
Catalog # [630013](#)

Standard Kelly Bar Adapter 10,000 Ft Lbs (13,558 N-M) for 2" (50.8 mm) Hex Kelly Bar.



Features

- Kelly Bar Adapter attaches to truck's torque motor drive shaft (Kelly Bar)
- Locking Dog Assembly has six holes for 1/2" bolts on a 5-1/4" bolt circle, comes with six 1/2" Grade 5 bolts, nuts and lock washers
- Painted with green paint
- Includes Bent Arm Pin and Coil Lock

Application

Anchor/Pile Installation

General

Bolt Grade	5
Coating	Painted
EU RoHS Indicator	No
Kelly Bar Shape	Hex
Number of Bolt Holes	6
Torque Rating	10000 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359227441

Dimensions

Anchor Installation Hole Size	0.5 in
Diameter - Bolt	0.5 in
Diameter - Bolt Circle	5.25 in
Dimensions	7.310 in x 6.500 in x 7.310 in
Height	7.310 in
Kelly Bar Adapter Inside Width	2 in
Kelly Bar Hole Distance to Flange	5 in
Length	7.310 in
Weight	9.800 lb
Width	6.500 in

Logistics

Pallet Quantity	80
Standard Package	1

Product Assets

[Catalogs - Anchor Tools \(4A_CA06122E\)](#)
[Installation Manuals - Instructions for CHANCE Kelly Bar Adapters \(P3031465\)](#)
[Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
[Literature - Anchoring \(CA12002E\)](#)
[Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide \(BR06167E\)](#)
[Sales Drawings - 2" Hex Kelly Bar \(SA630013\)](#)
[Technical Solutions - CH-630013-SPEC-EN](#)
[Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

Related Products

[P0010259P - Anchor Tool Bolt](#)
[O55635P - Anchor Tool Nut](#)
[C3031223 - Anchor, Tool, Bent Arm Pin, 1/2in X 4.5in](#)
[O55371P - Anchor Tool Lockwasher](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-630013-SPEC-EN | REV 1/2024