



Anchor, No Wrench, 6in x 66in Thimbleye

By Chance
Catalog # [63461](#)

No-Wrench 66" (1676 mm) long with 6" (152 mm) Helix Thimbleye.



Features

- No-Wrench Screw Anchors may be installed by hand or machine.
- Hot dipped galvanized per ASTM A153
- No-Wrench Screw Anchors can be installed to a greater depth to reach a firmer soil by using an extension rod

General

Application	Helical Anchoring
Catalog Number	63461
Coating	Galvanized, ASTM A-153
Eye Nut Style	Thimbleye
Number of Helices	1
Torque Rating	400 ft-lbs
Type	Helical Anchors
UPC	096359072997

Dimensions

Anchor Helix Diameter(s)	6 in
Dimensions	66.000 in x 6.000 in x 6.000 in
Height	6 in
Length	66 in
Rod Diameter	0.75 in
Weight	10 lb
Width	6 in

Logistics

Pallet Quantity	100
Standard Package	1

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - No Wrench Anchors](#)
- [Installation Manuals - Holding Capacity Chart for No-Wrench Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance Literature - Anchoring](#)
- [Sales Drawings - No Wrench Screw Anchor & Extension](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE No Wrench](#)



A Hubbell brand