



Guy Clamp, 3-Bolt, 5/16in to 1/2in Strand Size

By CHANCE Utility
Catalog # [6461](#)

Parallel grooves of clamp body tightly traps strand to form a loop type guy deadend.



Features

- Three 5/8" dia. clamping bolts
- 1-21/32" x 6" clamping plates
- Galvanized steel per ASTM A-153
- RUS Listed, u - Deadend for steel or aluminum clad strand

General

Coating	Galvanized, ASTM A-153
Material	Steel
Type	Guy Deadend
UPC	096359073260

Dimensions

Distance From Pole	N/A
Weight	2.4 lb
Width	1.66 in

Certifications and Compliance

Industry Standard(s)	NEMA PH 23
RUS Listed Reference	u - Deadend for steel or aluminum clad strand

Logistics

Pallet Quantity	960
-----------------	-----

Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)
[Catalogs - Pole Line Hardware](#)
[Installation Manuals - CHANCE® Guy Clamp Instructions](#)
[Sales Drawings - Heavy Type Guy Clamp \(SA6461\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-6461-SPEC-EN | REV 7/2023