



EYENUT, STANDARD, 5/8"

By Chance
Catalog # [6502](#)

Standard eyenut that fits 5/8" diameter bolts. Most commonly used for deadending, back-guying, and attaching pole head guys on the threaded ends of crossarm bolts. Drop-forged hot dip galvanized steel. RUS Listed.

Features

- Tensile strength rating is 13,550 lbs
- Meets the requirements of ANSI C135.5

General

Catalog Number	6502
Coating	Galvanized, ASTM A-153
Material	Steel
Type	Eyenuts
UPC	096359073369

Dimensions

Dimensions	3.250 in x 2.500 in x 1.375 in
Distance From Pole	NA
Height	1.375 in



Length	3.25 in
Weight	0.66 lb
Width	2.5 in

Certifications And Compliance

Industry Standard(s)	ANSI C135.5
RUS Listed Reference	aa - Nut, eye

Logistics

Pallet Quantity	2400
-----------------	------

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Pole Line Hardware](#)
- [Sales Drawings - Eyenut](#)
- [Specifications - 6502](#)



A Hubbell brand