



Anchor, PISA Nut 1in threads Thimbleye

By CHANCE Utility
Catalog # 6512

Thimbleye eyenut for 0.75" (19.1 mm) & 1" (25.4 mm) Pisa Rod.



*Representative Image

Features

- For use the Pisa style anchor rods
- Eyes are dropped forged for better strength and reliability
- Hot dipped galvanized per ASTM A153

Application

Helical Anchoring

General

Coating	Galvanized, ASTM A-153
Eyenut Style	Thimbleye
Material	Steel
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	33500 lb
Type	Power Installed Screw Anchor (PISA)
UPC	096359073406

Dimensions

Distance From Pole	N/A
Rod Diameter	<ul style="list-style-type: none"> • 0.750 • 1.000 in
Weight	1.911 lb

Certifications and Compliance

RUS Listed Reference	z - Anchors, screw, power installed
----------------------	-------------------------------------

Logistics

Pallet Quantity	960
Standard Package	25

Product Assets

- [Catalogs - Communications Catalog \(CA12042E\)](#)
- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06131E_PISA_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - Nut, Thimbleye \(SA6512\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Tough One and PISA Anchor Installation \(VI0645E\)](#)
- [Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

Related Products

- [12334P - Anchor, PISA Rod, 1in X 7ft, 1in threads](#)
- [12632P - Anchor, PISA Rod, 3/4in X 7ft, 1in threads](#)
- [G5068 - Thimbleye® ANCHOR ROD BONDING CLAMP for 3/4in & 1in PISA RODS](#)



A proud member of the Hubbell Family.