



Anchor, PISA Nut, 1in threads Twineye 50kip capacity

By CHANCE Utility
Catalog # 6562H



High strength Twineye eyenut for 1" (25.4 mm) Pisa Rod.

Features

- For use with the Pisa style anchor rods
- Eyes are dropped forged for better strength and reliability
- Hot dipped galvanized per ASTM A153
- Painted Orange

Application

Helical Anchoring

General

| | |
|------------------|--|
| Coating | Galvanized, ASTM A-153 |
| Eyenut Style | Twineye |
| Strength Note | Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength. |
| Tensile Strength | 50000 lb. |
| Type | Power Installed Screw Anchor (PISA) |
| UPC | 096359073550 |

Dimensions

| | |
|--------------|----------|
| Rod Diameter | 1.000 in |
| Weight | 1.862 lb |

Logistics

| | |
|------------------|------|
| Pallet Quantity | 1280 |
| Standard Package | 25 |

Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06131E_PISA_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - Twineye Nut \(SA6560\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Tough One and PISA Anchor Installation \(VI0645E\)](#)
- [Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

Related Products

- [C1021987 - Anchor, PISA Rod, 1in X 3.5ft 50kip rating, 1in threads](#)
- [C1021986 - Anchor, PISA Rod, 1in X 7ft 50 kip rating, 1in threads](#)
- [G5069 - Twineye® ANCHOR ROD BONDING CLAMP for 5/8in, 3/4in & 1in PISA RODS and 1in EXPANDING, CROSSPLATE & ROCK ANCHOR RODS](#)



A proud member of the Hubbell Family.