



Rod, Expanding/Cross-Plate Anchor, 3/4in X 9ft Tripleye

By CHANCE Utility
Catalog # 7559

Expanding/Cross-Plate Anchor Rod 0.75" (19.1 mm) Diameter
Rod, 9' (2743 mm) long with Tripleye.



*Representative Image

Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153
- Square nut assembled to rod
- Rods used with Cross-plate and Expanding anchors

Application

Earth Tension Anchoring

General

Coating	Galvanized, ASTM A-153
Eyenum Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	23000 lb.
Type	Anchor Rod
UPC	096359074373

Dimensions

Length	108.000 in
Rod Diameter	0.750 in
Weight	14.043 lb

Logistics

Pallet Quantity	60
Standard Package	3

Product Assets

[Catalogs - Anchors \(4\)](#)
[Installation Manuals - TD06135E_Expanding_Anchors](#)
[Installation Manuals - TD06136E_Cross_Plate_Anchors](#)
[Literature - Anchoring \(CA12002E\)](#)
[Sales Drawings - SA7557](#)
[Sales Drawings - Threaded Tripleye Rod 3/4" \(SA7556\)](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Video - CHANCE Expanding Anchors \(VI0642E\)](#)

Related Products

[55312P - Nut, Expanding/Cross-Plate Anchor Rod](#)
[G5063 - Tripleye® ANCHOR ROD BONDING CLAMP for 3/4in & 1in EXPANDING, CROSSPLATE NO-WRENCH & ROCK ANCHORS](#)



A proud member of the Hubbell Family.