



# Rod, Expanding/Cross-Plate Anchor, 1-1/4in X 10ft Tripleye

By Chance  
Catalog # 7574

Expanding/Cross-Plate Anchor Rod 1.25" (31.7 mm) Diameter Rod, 10' (3048 mm) long with Tripleye.



## Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153
- Square nut assembled to rod
- Rods used with Cross-plate and Expanding anchors

## General

Application	Earth Tension Anchoring
Catalog Number	7574
Coating	Galvanized, ASTM A-153
Eyenuit Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	58000 lb.
Type	Anchor Rod
UPC	096359074410

## Dimensions

Dimensions	120.000 in x 3.000 in x 2.000 in
Height	2 in
Length	120 in
Rod Diameter	1.25 in
Weight	42.042 lb
Width	3 in

## Logistics

Pallet Quantity	50
Standard Package	1

## Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06136E\\_Cross\\_Plate\\_Anchors](#)
- [Installation Manuals - TD06135E\\_Expanding\\_Anchors](#)
- [Literature - Anchoring](#)
- [Sales Drawings - Threaded Tripleye Rod -1 -1/4"](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Expanding Anchors](#)

