



BOLT, SPOOL, SINGLE-UPSET, 5/8in x 10in

By Chance
Catalog # [7742](#)

Spool bolts are used to support a spool insulator in the horizontal position in secondary applications. Industry slang is Upset Bolt.



Features

- 4" thread length and cone pointed end
- Overall length is 14-3/4"
- Includes one square nut with cotter key
- Rated cantilever load is 1,900 lbs.
- Hot dip galvanized per ASTM A-153
- Manufactured in compliance with ANSI C135.31
- RUS listed, q - Bolt, double upset

General

Catalog Number	7742
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb.
Type	Single Upset
UPC	096359074441

Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Dimensions	15.000 in x 1.750 in x 1.750 in
Distance From Pole	N/A
Height	1.75 in
Length	15 in
Length - Threaded Area	4
Weight	1.5 lb
Width	1.75 in

Certifications And Compliance

RUS Listed Reference	bs - Bolt, single upset
----------------------	-------------------------

Logistics

Pallet Quantity	1500
-----------------	------

Product Assets

[Catalogs - Pole Line Hardware](#)
[Sales Drawings - Upset Spool Bolts Single And Double](#)



A Hubbell brand