



BOLT, MACHINE, SQ HEAD, 3/8in x 4in

By CHANCE Utility
Catalog # [8604](#)



Square head machine bolt for utility pole and crossarm construction. Rated for 4,250 lbs. tensile strength. Includes one assembled square nut, cone point and 3" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	4250 lb.
Type	Machine Bolts
UPC	096359075035

Dimensions

Diameter	0.38 in
Diameter (Fraction)	3/8 in
Length	4.00 in
Length - Threaded Area	3
Weight	0.15 lb

Logistics

Pallet Quantity 15000

Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)
[Catalogs - Machine Bolts & DA Bolts \(5-53Supp24-28\)](#)
[Sales Drawings - Bolts, Machine 3/8" \(SA8604\)](#)

Related Products

[PS6801 - WASHER, ROUND, 7/16in HOLE, 1in DIA.](#)
[3510 - MF TYPE CURVED LOCK NUT, 3/8in THREAD](#)
[C2050188 - SPRING WASHER, REGULAR-DUTY DOUBLE-COIL, 3/8in SIZE](#)
[8205 - HOUSE BRACKET, TYPE L](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-8604-SPEC-EN | REV 1/2024