



## CARRIAGE BOLT, 3/8in x 6in, 4,250 RATED TENSILE STRENGTH

By CHANCE Utility  
Catalog # [8636](#)

Square neck of the round head carriage bolt makes the bolt self-locking during tightening, when mated with a square hole. Offered in a variety of sizes. Commonly referred to as a coach bolt.



\*Representative Image

### Features

- 3" thread length
- Includes one square nut
- Rated tensile strength is 4,250 lbs
- Galvanized per ASTM A-153
- Manufactured in compliance with standards ANSI C135.1 and CAO 7096
- RUS listed, i - bolt carriage.

### General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	4250 lb.
UPC	096359075141

### Dimensions

Diameter	0.38 in
Diameter (Fraction)	3/8 in
Distance From Pole	N/A
Length	6.00 in
Length - Threaded Area	1.75
Weight	0.18 lb

### Certifications and Compliance

RUS Listed Reference                      i - Bolt, carriage

### Logistics

Pallet Quantity                              12000

### Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)

[Catalogs - Pole Line Hardware](#)

[Sales Drawings - 3/8" Carriage Bolt \(SA8634\)](#)

### Related Products

[PS6801 - WASHER, ROUND, 7/16in HOLE, 1in DIA.](#)

[3510 - MF TYPE CURVED LOCK NUT, 3/8in THREAD](#)

[C2050188 - SPRING WASHER, REGULAR-DUTY DOUBLE-COIL, 3/8in SIZE](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-8636-SPEC-EN | REV 4/2023