



BOLT, MACHINE, SQ HEAD, 1/2in x 14in



By Chance
Catalog # [8714](#)

Square head machine bolt for utility pole and crossarm construction. Rated for 7,800 lbs. tensile strength. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1

General

Catalog Number	8714
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	7800 lb.
Type	Machine Bolts
UPC	096359075318

Dimensions

Diameter	0.5 in
Diameter (Fraction)	1/2 in

Distance From Pole	N/A
Length	14 in
Length - Threaded Area	6 in
Weight	0.74 lb

Certifications And Compliance

RUS Listed Reference	c - Bolt, machine
----------------------	-------------------

Logistics

Pallet Quantity	3000
-----------------	------

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - Bolts, Machine 1/2"](#)
- [Specifications - 8714](#)



A Hubbell brand