



DOUBLE-ARMING BOLT, 3/4in x 22in w/4 NUTS



By Chance
Catalog # 8892

Full thread double-arming bolt for utility pole double arm construction. Rated for 18,350 lbs. tensile strength. Includes four assembled square nuts and cone point. Industry slang is DA bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1
- RUS listed, n - Bolt, double arming

General

Catalog Number	8892
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb.
UPC	096359075851

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Dimensions	22.625 in x 1.125 in x 1.125 in

Distance From Pole	N/A
Height	1.125 in
Length	22.625 in
Weight	2.87 lb
Width	1.125 in

Certifications And Compliance

Industry Standard(s)	ANSI C135.1
RUS Listed Reference	n - Bolt, double arming

Logistics

Pallet Quantity	600
-----------------	-----

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - Double-Arming Bolt](#)
- [Specifications - 8892](#)



A Hubbell brand