



BOLT, MACHINE, SQ HEAD, 3/4in x 10in



By Chance
Catalog # 8910

Square head machine bolt for utility pole and crossarm construction. Rated for 18,350 lbs. tensile strength. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1
- RUS listed, c - Bolt, machine

General

Catalog Number	8910
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb.
Type	Machine Bolts
UPC	096359075929

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Dimensions	10.750 in x 1.125 in x 1.125 in

Distance From Pole	N/A
Height	1.125 in
Length	10.75 in
Length - Threaded Area	6 in
Weight	1.34 lb
Width	1.125 in

Certifications And Compliance

Industry Standard(s)	ANSI C135.1
RUS Listed Reference	c - Bolt, machine

Logistics

Pallet Quantity	1440
-----------------	------

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - 3/4 Machine Or Crossarm Bolt](#)
- [Specifications - 8910](#)



A Hubbell brand