



# BOLT, MACHINE, SQ HEAD, 3/4in x 20in



By Chance  
Catalog # 8920

Square head machine bolt for utility pole and crossarm construction. Rated for 18,350 lbs. tensile strength. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

### Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1
- RUS listed, c - Bolt, machine

Distance From Pole	N/A
Height	1.125 in
Length	20.75 in
Length - Threaded Area	6 in
Weight	2.47 lb
Width	1.125 in

### General

Catalog Number	8920
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb.
Type	Machine Bolts
UPC	096359075974

### Certifications And Compliance

RUS Listed Reference	c - Bolt, machine
----------------------	-------------------

### Logistics

Pallet Quantity	960
-----------------	-----

### Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Dimensions	20.750 in x 1.125 in x 1.125 in

### Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - 3/4 Machine Or Crossarm Bolt](#)
- [Specifications - 8920](#)