



BOLT, MACHINE, SQ HEAD, 3/4in x 24in



By Chance
Catalog # 8924

Square head machine bolt for utility pole and crossarm construction. Rated for 18,350 lbs. tensile strength. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1
- RUS listed, c - Bolt, machine

Distance From Pole	N/A
Height	1.125 in
Length	25 in
Length - Threaded Area	6 in
Weight	2.81 lb
Width	1.125 in

General

Catalog Number	8924
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb.
Type	Machine Bolts
UPC	096359075998

Certifications And Compliance

RUS Listed Reference	c - Bolt, machine
----------------------	-------------------

Logistics

Pallet Quantity	600
-----------------	-----

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Dimensions	25.000 in x 1.125 in x 1.125 in

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - 3/4 Machine Or Crossarm Bolt](#)
- [Specifications - 8924](#)