



## BOLT, MACHINE, SQ HEAD, 3/4in x 28in

By CHANCE Utility  
Catalog # [8928](#)



Square head machine bolt for utility pole and crossarm construction. Rated for 18,350 lbs. tensile strength. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

### Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1

### General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb
Type	Machine Bolts
UPC	096359076018

### Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Distance From Pole	N/A
Length	28.00 in
Length - Threaded Area	6
Weight	3.23 lb

### Logistics

Pallet Quantity 420

### Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)  
[Catalogs - Machine Bolts & DA Bolts \(5-53Supp24-28\)](#)  
[Sales Drawings - 3/4 Machine Or Crossarm Bolt \(SA8908\)](#)

### Related Products

[C2050187 - SPRING WASHER, REGULAR-DUTY DOUBLE-COIL, 3/4in SIZE](#)  
[3513 - MF TYPE CURVED LOCK NUT, 3/4in THREAD](#)  
[6814 - WASHER, SQ FLAT, 3/4in SIZE, 2 1/4in](#)  
[6823 - WASHER, SQ CURVED, 7/8in HOLE, 3in SQ](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-8928-SPEC-EN | REV 4/2023