



BOLT, MACHINE, SQ HEAD, 3/4in x 30in



By Chance
Catalog # 8930

Square head machine bolt for utility pole and crossarm construction. Rated for 18,350 lbs. tensile strength. Includes one assembled square nut, cone point and 8” thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1

General

Catalog Number	8930
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb.
Type	Machine Bolts
UPC	096359488934

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Dimensions	30.875 in x 1.125 in x 1.125 in

Distance From Pole	N/A
Height	1.125 in
Length	30.875 in
Length - Threaded Area	8
Weight	3.5 lb
Width	1.125 in

Certifications And Compliance

RUS Listed Reference	c - Bolt, machine
----------------------	-------------------

Logistics

Pallet Quantity	420
-----------------	-----

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - 3/4 Machine Or Crossarm Bolt](#)
- [Specifications - 8930](#)