



# Anchor, Adapter, SS5/SS150 Thimbleye

By CHANCE Utility  
Catalog # [C1020023](#)

Square Shaft & Round Rod Guy Adapter Thimbleye.



## Features

- Guy adapters include a high-strength bolt and nut.
- Forged fittings on both ends of adapters
- Hot dipped galvanized per ASTM A153

## Application

Helical Anchoring

## General

Coating	Galvanized
Eyenuit Style	Thimbleye
Finish Type	Galvanized
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Type	Adapters
UPC	096359008279

## Dimensions

Dimensions	18.00 in x 3.500 in x 2.500 in
Height	2.500 in
Length	18.00 in
Weight	10.584 lb
Width	3.500 in

## Logistics

Pallet Quantity	200
Standard Package	5

## Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06132E\\_Type\\_SS\\_and\\_RR\\_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Forged Pulling Eye \(SF06013E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - Rock Anchor Assembly \(SA1040004\)](#)
- [Sales Drawings - Forged Guy Adapter \(SA1020024\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

## Related Products

- [P0010041P - Square Shaft \(SS5/SS150\) Hardware](#)
- [055449P - Square Shaft \(SS5/SS150\) Nut](#)



A proud member of the Hubbell Family.