



Anchor, Adapter, SS5/SS150 Tripleye no pulling eye

By Chance

Catalog # [C1020025A](#)

Square Shaft & Round Rod Guy Adapter Tripleye.



Features

- Guy adapters include a high-strength bolt and nut.
- Forged fittings on both ends of adapters
- Hot dipped galvanized per ASTM A153

General

Application	Helical Anchoring
Catalog Number	C1020025A
Coating	Galvanized, ASTM A-153
Eyenuit Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Type	Adapters
UPC	096359579113

Dimensions

Dimensions	18.000 in x 3.500 in x 3.000 in
Height	3 in
Length	18 in
Weight	9.565 lb
Width	3.5 in

Logistics

Carton Quantity	5
Pallet Quantity	200
Standard Package	5

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Literature - Forged Pulling Eye](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Sales Drawings - Forged Guy Adapter](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process](#)
- [Video - CHANCE Square Shaft Anchor Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C1020025A-SPEC-EN | REV 6/2024