



Anchor, Disk, 16in X .187in, fits 3/4in rod

By CHANCE Utility
Catalog # [C1022008](#)

Corrosion-Resistant Anchor .187" (4.7mm) Thick for 16" (406 mm) Hole used with 0.75" (19.1 mm) Diameter Rod.



*Representative Image

Features

- Designed to be used with Protected Anchor Rods, Fiber Washer and Cap Nut
- Coated with black paint

Application

Earth Tension Anchoring

General

Coating	Black Paint
Type	Corrosion-Resistant Anchor Parts
UPC	096359008507

Dimensions

Anchor Hole Size	16 in
Rod Diameter - Order Separately	0.750 in
Thickness	0.187 in
Weight	12.524 lb

Logistics

Pallet Quantity	50
Standard Package	1

Product Assets

[Catalogs - Appendix A - Transmission And Substation Technical Design Manual \(TD_06_088_E\)](#)

[Catalogs - Anchors \(4\)](#)

[Installation Manuals - Holding Capacity Chart - Soil Classification](#)

[Installation Manuals - TD06134E_Corrosion_Protected_Disk_Anchors](#)

[Installation Manuals - Holding Capacity Chart - Corrosion Resistant Anchors](#)

[Literature - Anchoring \(CA12002E\)](#)

[Sales Drawings - Anchor \(SA1022008\)](#)

[SDS - MSDS - Galvanized Steel Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C1022008-SPEC-EN | REV 4/2023