



Anchor, Disk, 30in X .375in fits 1.25in rod

By CHANCE Utility
Catalog # [C1022381](#)

Corrosion-Resistant Anchor .375" (9.5 mm) Thick for 30" (762 mm) Hole used with 1.25" (31.75 mm) Diameter Rod.



Features

- Designed to be used with Protected Anchor Rods, Fiber Washer and Cap Nut
- Hot dipped galvanized per ASTM A153

Application

Earth Tension Anchoring

General

Coating	Black Paint
Type	Corrosion-Resistant Anchor Parts
UPC	096359590323

Dimensions

Anchor Hole Size	30 in
Rod Diameter - Order Separately	1.250 in
Thickness	0.375 in
Weight	72.708 lb

Logistics

Pallet Quantity	5
Standard Package	1

Product Assets

[Catalogs - Appendix A - Transmission And Substation Technical Design Manual \(TD_06_088_E\)](#)

[Installation Manuals - Holding Capacity Chart - Soil Classification](#)

[Installation Manuals - TD06134E_Corrosion_Protected_Disk_Anchors](#)

[Installation Manuals - Holding Capacity Chart - Corrosion Resistant Anchors](#)

[Literature - Anchoring \(CA12002E\)](#)

[Sales Drawings - 30 Inch Diameter Disk Anchor With 15 FT X 1-1/4 Inch 2 Pcs Rod \(SA1022381\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C1022381-SPEC-EN | REV 4/2023