



## Anchor, Tough One, 10in, 15,000 ft-lb rating, 2.5in hub, 1in threads

By CHANCE Utility  
Catalog # [C1025001](#)

Tough One Anchor Helix, 15,000 Ft Lbs (20,340 N-M), 10" (254 mm) Helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.



\*Representative Image

### Features

- Installed with Chance anchor wrench C3031064 or C3030983
- The anchor's sloped lead point improves penetration and helps soil flow from below the hub to above the anchor.
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

### Application

Helical Anchoring

### General

Coating	Painted
Number of Helices	1
Torque Rating	15000 ft-lbs
Type	Anchor Helix
UPC	096359008590

### Dimensions

Anchor Helix Diameter(s)	10 in
Anchor Hub Size	2.500 in
Rod Diameter	<ul style="list-style-type: none"><li>• 0.750</li><li>• 1.000 in</li></ul>
Weight	16.023 lb

### Logistics

Pallet Quantity	144
Standard Package	3

### Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Installation Manuals - TD06130E\\_Tough\\_One\\_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - PISA Anchors \(TD06166E\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Literature - How to Match Anchors and Installing Wrenches \(049114\)](#)
- [Sales Drawings - Tough One 10,000 & 15,000 \(SA1025000\)](#)
- [Video - CHANCE Tough One and PISA Anchor Installation \(VI0645E\)](#)
- [Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

### Related Products

- [C3030983 - Anchor, Tool, Drive End Wrench, Red Band, rated 15,000 ft-lbs, 7ft long](#)
- [C3031064 - Anchor, Tool, Drive End Wrench, Yellow Band, rated 10,000 ft-lbs, 7ft long](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-C1025001-SPEC-EN | REV 4/2023